



GOLDSTAR

FOUNTAIN SOLUTION

Goldstar is a gum based fountain solution for use on all litho presses whether web or sheetfed, large or small. It is formulated to give the ultimate performance in desensitisation holding open fine screens and hairline reversals like no other fount. Goldstar's versatility makes it also suitable for metal-dec / tin printing.

- Goldstar can be used successfully with all types of inks (including UV) and all types of metal plates. It is non-toxic and can be used in food packaging
- It contains powerful wetting agents which enable it to run with less water and, where applicable, less alcohol
- Goldstar contains agents, which speed ink drying and reduce blanket tackiness.
- Enables quicker start-ups, prints sharper half tones and reversals, gives denser solids and reduces paper waste
- Contains agents that help to prevent metal corrosion, mould growth and foaming
- Also available, Goldstar RO specifically for use with RO treated water

DIRECTIONS FOR USE:

Soft Water: Add 10-20 mls to 1 litre of water.

Hard Water: Add 20-40 mls to 1 litre of water.

The optimum dosage will vary with the type of press dampening system, water and work being printed and can only be arrived at after some experimentation and experience

